

Distributed by
Active Healthcare

Freecall 0800 336 3339
sales@activehealthcare.co.nz
www.activehealthcare.co.nz



Date:

Order No:

Number of pages:

Quote No:

Job No:

P/Slip No:

Frame colour: _____

Purchase Details:

Ph:

Fax:

Client Name

Contact No:

Standard Features using PG R-net

Centro-XT eXtreme terrain power wheelchairs are supplied with the following components as standard.

- Weight rating 175kg – AS3695 | Crash tested – AS 3696:19
- 50 Deg Power Tilt with Drive inhibit switch.
- PG R-Net **120amp PM** and **Colour** screen Joystick module.
- PG **ISM** for actuator use.
- Motors – **4 pole** 10 K/hr High Power 350 watt per motor)
- Castors **9" front** with **8" Rear** pneumatic
- Drive wheels - Aluminium Mag type with 14" Knobby Balloon - low pressure Pneumatic
- Seat Height 46cm 0-46 Tilt and 48cm 4-50 tilt. (Measured floor to top of seat rail at front of chair)
- Armrests Flip-up, adjustable height and with sliding arm pads.
- Choice of three colour finishes as standard (Many more as option refer to colour chart on our Web site)
- Vehicle Tie Down locations – Front & Rear
- Centre mount legrest

Centro-XT

☐ C-TSR-XT Centro Tilt Seat

Including Weight Shift 50 Deg Power Tilt

☐ C-ER-XT Centro Elite

As per TS with Weight Shift 50 Deg Power Tilt
+ 30 Deg Power Recline. PG ISM included

☐ C-VL-XT Centro Vertical Lift 50 deg

50 Deg Tilt + 30cm Vertical lift seat. PG ISM included -
49 seat height – *not available with Anterior tilt.*

☐ C-VLRB-XT Centro Vertical Lift 50 deg

50 Deg Tilt + 30cm Vertical Lift Seat + Power Reclining
Backrest + PG ISM
Included - 49 seat height - *not available with Anterior Tilt*

Low Seat Height OPTION 42cm

- ☐ 310560L Seat Base 42cm 0–46 deg Tilt in-lieu
of standard. (Measured from floor to top of seat
rail) Not available for VL.
Available in seat width 37cm and over
Custom seat frame for seat width under 37cm

Standard Colour choice

- ☐ Outback Red ☐ Island Blue ☐ Black Onyx
- ☐ 4015 Colour Surcharge
Specify Colour.....

Wheel Options

- ☐ 202715L 14" Wide Wheel (grey) - in lieu of Knobby tyre
(not available in Foam filled)
- ☐ 20170L Painted steel Drive wheels in lieu of Alum mag.
Colour

Centre Mount Foot Plate Options

- ☐ 310461 Calf Pads (Set) Centre mount foot plate.

Knee to Heel Dimensions

(foot plate to top of seat pan)

Specify Size _____ cm

- ☐ Custom Size Left _____ cm Right _____

Seat Width

- ☐ 31cm ☐ 34cm ☐ 37cm (extra small seat module)
☐ 37cm ☐ 40cm ☐ 43cm (small seat module)
☐ 43cm ☐ 46cm ☐ 49cm ☐ 52cm ☐ 55cm (standard seat module)
☐ 58cm ☐ 61cm ☐ 64cm (XL Custom P.O.A)
☐ 67cm ☐ 70cm ☐ 73cm (XXL Custom P.O.A)

Seat Depth

- ☐ 31cm ☐ 34cm ☐ 37cm (short)
☐ 40cm ☐ 43cm ☐ 46cm ☐ 49cm (standard)
☐ 49cm ☐ 52cm ☐ 55cm ☐ 58cm (Extended Actuator Mnt required for power Recline.) **See below**

☐ 310049-1L Extended Actuator Mnt - for seat depth (49 – 58cm)
Uses non-standard Back Canes and Mnt Brkts

☐ 61cm ☐ 64cm ☐ 67cm (not available with Power recline)

Motor and Drive Options

- ☐ 860110 PG Advance Stability Module
☐

Back Angle Recline 150

- ☐ 310475L Back angle (5 -60) Power Recline. In lieu of Std Power recline.
Note: Max seat depth 55cm

Seat & Tilt Options

- ☐ N/C Seat tilt 0 – 46 (footplate may interfere with castor wheel when in flat position) Refer to agent Rep
☐ N/C Seat tilt 4 – 50 Std (not avail on VL)
☐ 310261 Seat tilt 10 - 55 (P.O.A) (not avail on VL)
(Not available on VL)
☐ 310420 Raise Seat rail height 52cm
☐ 325501-(37-55) Seat Pan (Aluminium) 6mm to suit up to 55cm SD.
☐ 325502-(37-55) Seat Board (Vinyl Covered)

Seat Anterior Tilt Options

Note: Foot plate may touch ground or castor wheel when in negative tilt.

- ☐ 310260 Seat Tilt Anterior (-4 to 38 Deg) standard.
48cm seat height when tilted level.
When using Low seat frame -4 degree (SH 45cm when tilted level)

☐ 310263 L Seat Tilt Anterior (-7 to 26 Deg) Using Low Seat Frame. Seat height 48cm when tilted level. Uses 5 packing blocks.

R-net Controller Options



- ☐ 860076L Col to LED j/stick module **Downgrade**
☐ 860082 Dual Attendant control (must tick box below)
☐ 326971 Bracket - Attendant for above

☐ 860254 Knob 38mm ball
☐ 860251 Knob 80mm stick
☐ 860252 Knob 48mm Mushroom
☐ 860255 Knob 70mm Soft Ball
☐ 32699 J/Stick used as attendant (including mnt brkt)
☐ 860075D J/Stick module not required. (Must select master control unit. E.g. Omni)

Lighting Options

- ☐ 860073-LM PG Lighting module up grade –(lighting not included)
☐ 860073-K Lighting Kit (2 x LED head lights 1 x tail stop)
☐ LED Lighting Joy stick in lieu of LCD
☐ 860102L J/stick LCD with Speed Pot/Toggle/Lighting in lieu. (Toggle used for On/Off and Profile)

Controller Mounting Option and Placement

- ☐ 860521L Drop Down J-Stick Brk in lieu of std
☐ 326935L Swing away control bracket
☐ 310380L Retractable J/Stick bracket
☐ 310492L Joystick mnt brkt with cage R-net LCD

- ☐ Left hand side
☐ Right hand side
☐ Other

Speciality R-Net Controller Options

- ☐ 860078 Omni Module
☐ 860060 Bracket - Omni swivel/adjust mount bracket.
☐ 860060-G Goose neck mnt bracket Omni
☐ 860083 Remote Button Interface (If switching is required external of PG controller.
☐ 860088 Bluetooth PC mouse control
☐ 860103 Cable Bluetooth external switch 1
☐ 860103 Cable Bluetooth external switch 2
☐ 860087 Input / output Module

Batteries and Charger

- ☐ 506074 2 X Battery 75amp/hr (long distance)
☐ 50609-CTE Charger 8amp CTE.

Suspension Set up

APT suspension set up

- ☐ **Single** Spring – (Standard)
☐ **Double** spring
 for more information on suspension setup please refer to APT user guide.

Rear Spring

- ☐ **Type A** - Soft up to 120 kg (Standard)
☐ **Type B** - Hard 120 kg and over
Note: All spring types are a guide only.

Seating & Upholstery Options

FX Backrest Options

- ☐ 3397- (37 -55) FX Backrest Upholstery
 Specify Fabric with Std Fixed Mnt Bracket
- ☐ 310375 Quick release Mount Kit for FX Back
- Note: Specify Seat width on front page. require. 3397-37 to 3397-55 for costing.*
- ☐ Dartex (standard)
☐ Aero Mesh
☐ Vinyl Insert

Basic Back Upholstery Options

- ☐ 325401 Basic Backrest Upholstery, Foam over Ply
☐ Fabric Insert (standard)
☐ Vinyl Insert
- ☐ 33909 Bracket Multi holed for backrest mounting
- ☐ 33909 Wing Extension basic
☐ Left side ☐ Right side

Deluxe Backrest

Please Note: Deluxe Backs on Centro's with Power Recline Back can only be fitted with a maximum Seat Depth of 49cm using extended Actuator Mnt.

- ☐ 3390-(37-49) Deluxe Backrest Upholstery
☐ 3390-(52-55) Deluxe Backrest Upholstery
☐ 310432 Push handle (pram style)
☐ 310074 Bracket Multi holed for backrest mounting

- ☐ Dartex (standard)
☐ Vinyl Insert

Back Cane / Push Handle Options

- ☐ 310432 Pram Style Push handle
☐ Push handle removed (No Charge)
☐ 310190-C Custom Height Back Canes
☐ Floor to top (103cm Std) cm
☐ Back Cane height (58cm Std)cm
 from seat rail to top.
- ☐ 310438L Removable Back canes (non-recline ONLY)
☐ 310435L **Fold Down Back** (Only fitted in conjunction with either removable seat or removable Back upholstery with Back Strut fitted. Or Power Recl) Strut - If no power recline for F/down back.
- ☐ 325615
- ☐ Vinyl Insert

Knee to Heel Dimensions

(foot plate to top of Seat Pan)

- Specify Size cm
☐ Custom Size Left cm Right

Armrest

- ☐ N/C **Armrest Std height 31.5cm - 37cm**
☐ 310455L Armrest **Low** 24cm - 27cm
☐ 310456L Armrest **Intermediate** 26cm -29cm
☐ 310457L Armrest **Extra high** 35cm - 40cm
All measurements from seat frame to top of arm pad.
- ☐ 310430L Armrest, No Gap between back canes
 Standard pad only
- ☐ 310490 Armrest side panel (pair) for no-gap and gapped.
☐ 310491 Arm pad buffer bar (pair)
- ☐ 325602L Arm pad, Waterfall (not with no-gap Arms)
☐ 10655 Arm Trough, Swivel Bracket
☐ Right ☐ Left
- ☐ 10656 Arm Trough, Fixed Bracket
☐ Right ☐ Left
- ☐ 33160 Armrest **GLOVEBOX**
☐ Right ☐ Left

Headrests

- ☐ 32620 Headrest Deluxe, GLIDE with bracket and clamp
- ☐ 310204 Bracket welded on Spreader Bar
- ☐ 39305 Daher Combination Headrest (Pad only)
- ☐ 39300 Daher Large Headrest (Pad Only)

- ☐ 39301 Daher Lateral Support Headrest (Pad only)
- ☐ 39303 Daher Neck Rest (Pad only)
- ☐ 39302 Daher Small Headrest (Pad only)
- ☐ 39306 Daher Headrest Mounting Hardware
For use with above pads.

Lateral Supports

For Lateral Supports please use separate Lateral Support Order Form

Trays

- ❑ 1582 Tray, Flip up fold away
(Must be used in conjunction with drop down controller bracket)
 - ❑ 1583 Tray, Slide in
 - ❑ 15810 Frame only, For slide in tray no slides
 - ❑ 15820 Frame only for flip up fold away tray
 - ❑ 15840 Bracket, Slide in S8 armrest
- Please Note:** It is recommended that a Drop Down control bracket be used when trays are fitted.

Postural Support Options

Note: Not to be used as safety belt when transporting in motor vehicles.

- ☐ NB215I-A1 Seat Belt, Plastic buckle
☐ NB205L-A1 Seat Belt, Car Type Buckle
*Please use BodyPoint order form for other
 Restraint options.*

Wool Covers

Accessories

- ❑ 310395 Crutch holder (cylinder type)

Special Requirements: